


POS&POH grinding and polishing disc

Replacement for fine grinding and polishing



1. Introduction


The unique formula and the simultaneous action of diamond polishing fluid can not only achieve high removal rate, but also obtain perfect flatness and longer service life. Replaces traditional multiple grinding and polishing steps in a single step, increasing productivity and reducing preparation time.

2. Features

- POS&POH Two different hardness grades;
- Use with 0.25~15 μ m diamond polishing suspension;
- Maintains the flatness of coating;
- retain inclusions; – Higher efficiency.

3. Specifications

200mm, 250mm, 300mm, 350mm



4. Application

| Recommended abrasive particle size | Relative hardness | Recommended range | | |
|---------------------------------------|-------------------|-------------------|-----------|---------|
| | | < 150HV | 150~450HV | > 450HV |
| POS | Medium to low | ✓ | ✓ | × |
| POH | Medium to high | × | ✓ | ✓ |